
OSTSen-30102 User Guide



Ver 1.0

Onsystech

1. OSTSen-30102 Overview

OSTSen-30102 is a pulse oximetry and heart-rate monitoring module, which is based on Maxim Integrated MAX30102. The MAX30102 is an integrated pulse oximetry and heart-rate monitor modules. It includes internal LEDs, photodetector, optical elements, and low-noise electronics with ambient light rejection. The MAX30102 provides a complete system solution to ease the design-in process for mobile and wearable devices.

The MAX30102 operates on a single 1.8V power supply and a separate 5.0V power supply for the internal LEDs. Communication is through a standard I2C-compatible interface. The module can be shut down through software with zero standby current, allowing the power rails to remain powered at all times.

2. Application

- Wearable Devices
- Fitness Assistant Devices

3. Features

- Heart-Rate Monitor and Pulse Oximetry Sensor in LED Reflective Solution
- Tiny 5.6mm x 3.3mm x 1.55mm 14-Pin Optical Module
- Integrated Cover Digital Glass for Optimal, Robust Performance
- Ultra-Low Power Operation for Mobile Devices
- Programmable Sample Rate and LED Current for Power Savings
- Low-Power Heart-Rate Monitor (<1mW)
- Ultra-Low Shutdown Current (0.7uA typical)
- Fast Data Output Capability
- High Sample Rates
- Robust Motion Artifact Resilience
- High SNR
- -40°C to +85°C Operating Temperature Range


4. Application Information

4.1 Module Pin Out and Signal Description

Pin Number	Pin Name	Pin Description		
1	VCC	Power supply voltage (2.5V ~ 6V)		
2	GND	Power supply ground		
3	SCL	I2C Serial clock 7bit device address : 0x57		
4	SDA	I2C Serial data		
5	INT	Active-Low Interrupt (Open-Drain)		
8	V18	1.8V Voltage Output		
6,7	NC	Not Connect		

• MAX30102 I2C 7bit Device Address : 0x57


MSB							LSB
1	0	1	0	1	1	1	R/W



< Top View >


Pin Number	Pin Name	Pin Description
1,7,8,14	N.C.	No Connection
2	SCL	I2C Clock Input
3	SDA	I2C Clock Data, Bidirectional (Open-Drain)
4	PGND	Power Ground of the LED Driver Blocks
5	R_DRV	Red LED Driver
6	IR_DRV	IR LED Driver
9	VLED+	LED Power Supply(anode connection) Use a bypass
10	VLED+	capacitor to PGND for best performance
11	Vdd	Analog Power supply
12	GND	Analog Ground
13	INT	Active-Low Interrupt(Open-Drain)

4.2 MAX30101 Pin out and Signal Description



< MAX30102 Pinout (top view) >


5. Module Dimension





< OSTSen-30102 module >

6. Demo System



OSTSen-30102 Data Display on PC

RealTerm: Serial Capture Program 2.	0.0.70
$\begin{array}{llllllllllllllllllllllllllllllllllll$	4446 4459 1459 1454 1459
Mark	Qpen Spy Change Disconnect Software Flow Control RxD (2) Receive Xon Char: [17] ITXD (8) Traverse Vale Char: [3] CTS (8)
	Char Count:2073724 CPS:0

7. Reference

- 1) <u>https://www.maximintegrated.com/en/products/analog/sensors-and-sensor-interface/MAX30102.html</u>
- 2) https://datasheets.maximintegrated.com/en/ds/MAX30102.pdf
- 3) https://github.com/sparkfun/SparkFun_MAX3010x_Sensor_Library
- If you need more information or have some questions about OSTSen-30102, contact ostsen@naver.com.